





Signal Devices

Beacon Accessories



WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
Installation Beacon Accessories						
97581201		PDF	WERMA tube adapter, tube mount, 57mm diameter, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
97581202		PDF	WERMA surface mounting base, base mount, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
97581503		PDF	WERMA beacon enclosure, surface mount, 1 hole. For use with beacons with 37mm (PG 29) mounting installation.		Polycarbonate/ ABS blend	8.5 g [0.3 oz]
97581507		PDF	WERMA beacon enclosure, surface mount, 2 holes. For use with beacons with 37mm (PG 29) mounting installation.			14.17 g [0.5 oz]
97581508		PDF	WERMA beacon enclosure, surface mount, 3 holes. For use with beacons with 37mm (PG 29) mounting installation.			17g [0.6 oz]
97581522		PDF	WERMA anti-twist washer, stainless steel. For use with Werma beacons with 37mm (PG 29) mounting installation.		304 Stainless steel	0.57 g [0.02 oz]
Freestanding Beacon Accessories						
96000001		PDF	WERMA mounting bracket, tube mount, black, polyamide. For use with 50mm or 70mm terminal elements. M16 x 1.5mm cable gland included.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
97520901		PDF	WERMA plastic base with integrated tube, base mount, 70mm diameter, 110mm length, black, polyamide. For use with 209 or 219 series beacons.		Polyamide	0.1 lbs [1.6 oz]
97520902		PDF	WERMA cable gland, M25 x 1.5mm thread type, polyamide, black, accepts 8–17mm diameter cable, IP68.		Nylon	0.1 lbs [1.6 oz]
97582603		PDF	WERMA galvanized wire guard, steel. For use with 826, 827, 828 or 829 series industrial signal beacons.		Wire D 3mm, chromed	140g [4.93 oz]
97582605		PDF	WERMA mounting bracket, wall mount, black, ABS/ polycarbonate. For use with 826, 827, 828 and 829 series industrial signal beacons.		Polycarbonate/ ABS blend	62g [2.19 oz]





Signal Devices

Visual 98mm Base Mount Beacons

Features

- Choose from permanent incandescent, permanent LED, flashing Xenon, EVS (Enhanced Visibility System) flashing LED, and rotating models
- Base mount installation
- 98mm diameter
- Light-intensive Xenon flash in flash models
- Bulb not included with 826 incandescent models
- 25W bulb included with 827 incandescent models
- Various mounting accessories available
- 2-year warranty



Visual 98mm Base Mount Beacons 826, 827, and 828 Series Selection Chart

Part Number	Price	Color	Drawing link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals
74mm Base Mount													
82610000		Red	PDF	Incandescent Permanent Light 98mm	12-240 V AC/DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (bulb sold separately)	-				180 [6.35]		
82620000		Green	PDF										
82630000		Yellow	PDF										
82640000		Clear	PDF										
82650000		Blue	PDF										
82710075		Red	PDF	Incandescent Blinking Light (1.5 Hz blinking frequency, 5Ws flash energy) 98mm	24 VAC/VDC	max. 3.0 A		-4 to +122 °F [-20 to +50 °C] IP65 when mounted	Up to 5,000h	Polycarbonate cap Polycarbonate/ABS base	207 [7.30]	Terminal screws Max 2.5 mm ² AWG 16-14 Cable diameter 5-8 mm	cULus file E164155, CE, RoHS
82720075		Green	PDF										
82730075		Yellow	PDF										
82740075		Clear	PDF										
82750075		Blue	PDF										
82710077		Red	PDF	Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 98mm	115 VAC/VDC	max. 500 mA	≤ 3.0 A						
82720077		Green	PDF										
82730077		Yellow	PDF										
82740077		Clear	PDF										
82750077		Blue	PDF										
82810055		Red	PDF	Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 98mm	24 VDC	300 mA							
82820055		Green	PDF										
82830055		Yellow	PDF										
82840055		Clear	PDF										
82850055		Blue	PDF										
82810067		Red	PDF	Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 98mm	115 VAC	65 mA 50-60 Hz							
82820067		Green	PDF										
82830067		Yellow	PDF										
82840067		Clear	PDF										
82850067		Blue	PDF										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Bulbs



[95582635](#)

Bulbs						
Part Number	Price	Description	Wattage	Voltage	For Use With	Life Duration
95582635		Bulb for incandescent light BA15d bayonet socket	15W	24 VAC/DC	826xxxxx	up to 5,000h
95582637				115 VAC		
95582638				230 VAC		
95582735		Bulb for blinking incandescent light B15d bayonet socket	25W	24 VAC/DC	827xxxxx	up to 2,000h
95582737				115 VAC		
95588524		Halogen bulb G6.35	20W	12V	885xxx78	
95588525				24V	885xxx75	



[95582735](#)



[95588524](#)