



**Southwire™**

TOOLS & EQUIPMENT

# Wire Cutters/Pliers Strippers/Shears

## Overview

Southwire's pliers and cutters are made from American forged steel and assembled with hot rivet technology. These tools are built to withstand the wear-and-tear of any job. The inclusion of beveled cutting edges with heat-treated steel and comfortable handles make working with all gauges of wire and cable effortless.



Wire Cutters/Pliers/Strippers/Shears					
Part Number	Description	Tool Length	Qty/Pkg	Weight (lbs)	Price
<b><u>S1020SOLUS</u></b>	Southwire wire stripper/cutters, for cutting wire and stripping wire, beveled cutting edges, 6in overall length, padded comfort grip handles.	6in	1	0.31	\$12.00
<b><u>DCPA8D-US</u></b>	Southwire diagonal cutters, for cutting wire, induction hardened beveled cutting edges, 15-degree angled head, 8in overall length, comfort grip handles.	8in	1	0.63	\$35.75
<b><u>CCP9D-US</u></b>	Southwire cable shears, for cutting cable and wire, induction hardened shear cutting edges, 9in overall length, comfort grip handles.	9in	1	1.03	\$36.00
<b><u>SCP9TPCD-US</u></b>	Southwire linemans pliers, for cutting, crimper, fish tape pulling, and conduit and box reaming, induction hardened beveled cutting edges, 9in overall length, comfort grip handles.	9in	1	1.07	\$40.00
<b><u>TCC9D-US</u></b>	Southwire crimping pliers, crimps insulated and non-insulated terminals and connectors, induction hardened beveled cutting edges, 9in overall length, comfort grip handles.	9in	1	0.96	\$31.50



**S1020SOLUS**

- Strips and cuts up to 10-20 AWG solid and 12-22 AWG stranded wire
- Double-dipped grip for comfortable fit
- Serrated nose holds cable for easy twisting and pulling
- Spring-loaded for self-opening action



**DCPA8D-US**

- Effectively cuts most hardened wire, ACSR, bolts, screws and nails
- High-leverage design provides maximum cutting power
- Angled head allows for easy work in confined spaces



**CCP9D-US**

- Cuts up to 4/0 AWG aluminum, 2/0 AWG copper, and 100-pair 24 AWG communications cable
- Induction hardened blades for maximum durability
- Dipped handles for comfort



**SCP9TPCD-US**

- High-leverage design provides maximum cutting power
- Induction hardened cutting blades ensure efficient and lasting cutting surfaces for hard and soft wire
- Features a crimper, fish tape puller and reaming head for added versatility



**TCC9D-US**

- Crimps insulated and non-insulated terminals and connectors
- Specially hardened wire cutter in nose
- Tapered nose for working in confined spaces



**Southwire™** | TOOLS & EQUIPMENT

# Cable Shears and Pliers

## Overview

Southwire's cable shears and pliers are built to withstand wear-and-tear of any job. The inclusion of beveled cutting edges with heat-treated steel and comfortable handles make working with all gauges or wire and cable effortless.

Cable Shears and Pliers					
Part Number	Description	Tool Length	Qty/Pkg	Weight (lbs)	Price
<b>MP61</b>	Southwire crimping pliers, for cutting cables, cutting copper and brass screws, stripping wire, and crimping insulated and non-insulated terminals and connectors, beveled cutting edges, 9in overall length, comfort grip handles.	9in	1	0.49	\$25.00



**MP61**

## Features

- Strips and cuts: 8-22 AWG solid or 10-24 AWG stranded
- Crimps: insulated and non-insulated terminals/connectors
- Shears & re-threads: 10-24, 10-32, 8-32, 6-32, and 4-40 screws



**Southwire™** | TOOLS & EQUIPMENT

# Screwdriver and Nutdriver Sets

Retired: Please consider p/n 05018283055 as a replacement.



**SDSET8US**



## SDSET8US Screwdriver Set

- An 8 piece set that includes: 1/4" cabinet tip with 4" shank, 3/16" cabinet tip with 4" shank, 3/16" cabinet tip with 6" shank, 1/4" keystone tip with 4" shank, 5/16" keystone tip with 6" shank, #1 phillips head with 3" shank, #2 phillips with 4" shank, and #2 square tip with 4" shank
- Proudly made in the USA
- Larger cushion grip handle provides ultimate comfort and great torque
- Tether holes provided in handles for tether/lanyard attachment
- Handle end is marked for easy identification of tip type and size

Screwdriver Sets				
Part Number	Description	Pcs/Pkg	Weight (lbs)	Price
<b>SDSET8US</b>	Southwire screwdriver set, 8 pieces, imperial.	4	2.16	Retired

Retired: Please consider p/n 05345230055 as a replacement.



**NDSET7-US**



**ND6N1HD**

## NDSET7-US Nutdriver Set

- 7 piece set includes: 1/2", 1/4", 3/8", 5/16", 7/16", 3/16", and 11/32" nut drivers
- Proudly made in the USA
- Hollow shaft for screw clearance
- Larger cushion grip handle provides ultimate comfort and great torque
- Nut drivers for the most used nut and bolt sizes
- Tether holes provided in handles for tether/lanyard attachment
- Handles marked for easy identification

## Multi-driver

- 6 IN 1 Multi-driver with 3/16", 1/4", 5/16", 3/8", 7/16", 9/16" nut drivers.
- Heavy Duty steel shanks with bolsters for wrench assisted turning
- Comfort grip handle provides extra comfort and maximum torque
- Color coded ends for quick identification of sizes
- Chrome plated finish for corrosion resistance
- Hollow shafts for screw clearance

Nut Drivers and Sets				
Part Number	Description	Pcs/Pkg	Weight (lbs)	Price
<b>NDSET7-US</b>	Southwire nutdriver set, 7 pieces, imperial.	7	1.95	Retired
<b>ND6N1HD</b>	Southwire nutdriver, 4 pieces, imperial.	4	1	\$20.50


**Southwire™**

TOOLS &amp; EQUIPMENT

# Fish Tape

## Overview

Southwire's SIMpull™ fish tape makes pulling wire or cable through a filled or empty conduit up to 2 inches in diameter easily. The low friction design allows these fish tapes to easily glide through the conduit without binding at turns, joints, or couplings. Spiral extruded polymer reduces the amount of effort required to push or pull the fish tape through EMT, IMC, Rigid or PVC conduit and as an added bonus polymer fish tapes will not rust. Do not confuse these polymer tapes with a fiberglass tape. A polymer fish tape offers greater flexibility than fiberglass tapes. These fish tapes will not break when folded or leave uncomfortable splinters. With the swiveling flexible metal leader and the polymer non-conductive tape makes the job SIMpull.

## Features

- Spiral extruded polymer design reduces the amount of effort required to push or pull the fish tape.
- Swiveling flexible metal leader easily glides through bends
- Low friction material reduces binding at joints, couplings, or 90-degree bends
- Two lengths 75 or 125 feet
- 580 lbs. tensile strength
- 4.5mm diameter tape
- Weighs less than a steel tape


**FTSP45-75FML**

**FTSP45-125FML**

Fish Tape				
Part Number	Description	Pcs/ Pkg	Weight (lbs)	Price
<b><u>FTSP45-75FML</u></b>	Southwire SIMpull fish tape, 75ft length, spiral extruded polymer, swiveling flexible metal leader, 580lb tensile strength.	1	2.77	\$66.00
<b><u>FTSP45-125FML</u></b>	Southwire SIMpull fish tape, 125ft length, spiral extruded polymer, swiveling flexible metal leader, 580lb tensile strength.	1	3.35	\$96.00



**Southwire™**

TOOLS & EQUIPMENT

# Misc Sets



**60010S**

## Features

- UL listed CAT IV 600V, CAT III 1000V Test Leads
- 39in test leads
- 1000V AC/DC (Max)
- 10 Amp Current (Max)
- Includes removable CAT III 600V Alligator Clips

Miscellaneous Sets				
Part Number	Description	Pcs/Pkg	Weight (lbs)	Price
<b>60010S</b>	Southwire test lead set, CAT IV 600V/CAT III 1000V, 48in length. Alligator clip adapters included.	1	0.31	\$17.00


**Southwire™**

TOOLS &amp; EQUIPMENT

# Tool Accessories


**BAGESP**

## Electrician's Shoulder Pouch

- Lightweight, durable bag that can be carried, slung over your shoulder or attached to a belt.
- 11 inside and 5 outside for a total of 16 tool storage pockets
- Side pocket with Flip Lid™ Spill Guard provides secure easy access to small parts such as wire nuts or screws
- 3 different carrying options: Padded shoulder strap, tunnel loop for belt access, or padded handle
- Constructed from 2400d ballistic weave for durability
- Electrical Tape Strap
- Adjustable Hammer/Flashlight Loop
- Two rubber feet keep it stable when setting on a workbench or out on the factory floor.

## EDGEFORCE™ Hawk Bill Knife


**HBKND2**

- Premium D2 Stainless Steel Holds an edge
- Curved blade for pull cuts and splicing
- Rugged metal handle
- Stonewash black oxide coated blade
- Liner lock keeps blade secure
- Comfort grip for maximum hold and comfort
- Reversible belt clip

## Folding Utility Knife


**UTILQO**

- Quick open button for easy one hand operation
- Durable metal body with comfort grip for secure hold
- Easy blade replacement
- Rugged metal handle
- Comfort grip for maximum hold and comfort
- Quick open/close button
- Lanyard hole
- Belt clip

### Accessories Selection

Part Number	Description	Weight (lbs)	Price
<b>BAGESP</b>	Southwire tool bag, 2400 denier ballistic weave nylon, 16 compartments.	2	\$42.50
<b>HBKND2</b>	Southwire EDGEFORCE folding knife, hawkbill, 2.60in blade length, 7.24in overall length, metal body with comfort grip and pocket clip.	0.3	\$28.50
<b>UTILQO</b>	Southwire EDGEFORCE folding knife, common replaceable 2 point utility blade, utility blade length, 6.01in overall length, metal body with comfort grip and pocket clip.	0.4	\$12.50