



Ratchets & Sockets



Impact Sockets — 3/8in Drive

Titan 3/8in drive impact sockets cover the most common general-purpose fastening. Forged chrome-vanadium steel with a black manganese-phosphate finish resists impact and corrosion, and 6-point openings grip fasteners without rounding in SAE and metric, standard, and deep.

Features

- Impact-rated 6-point design maximizes grip and resists rounding
- Chrome-vanadium steel with manganese-phosphate anti-corrosion finish
- Standard and deep lengths for flush and protruding fasteners
- SAE and metric sizes



Impact Sockets — 3/8in Drive						
Part Number	Product Image	Pcs.	Measurement	Socket Type	Set Includes	Price
T48001		9	Imperial	Standard	(8) impact sockets (5/16in, 3/8in, 7/16in, 1/2in, 9/16in, 5/8in, 11/16in, and 3/4in), (1) wobble adapter 1/4in hex, rubber storage holder	\$19.00
T48301		9	Imperial	Deep	(8) deep impact sockets (5/16in, 3/8in, 7/16in, 1/2in, 9/16in, 5/8in, 11/16in, and 3/4in), (1) wobble adapter 1/4in hex, rubber storage holder	\$20.00
T48201		9	Metric	Standard	(8) impact sockets (8mm, 10mm, 12mm, 13mm, 14mm, 15mm, 17mm, and 18mm), (1) wobble adapter 1/4in hex, rubber storage holder	\$19.00
T48401		9	Metric	Deep	(8) deep impact sockets (8mm, 10mm, 12mm, 13mm, 14mm, 15mm, 17mm, and 18mm), (1) wobble adapter 1/4in hex, rubber storage holder	\$20.00
T48300		12	Imperial	Deep	(12) deep impact sockets (5/16in, 3/8in, 7/16in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in, 13/16in, 7/8in, 15/16in, and 1in), plastic storage case	\$60.00