



Ratchets & Sockets



Torsion Impact Bit Set

The Titan 50-piece torsion impact bit set delivers professional driving performance for impact drivers. Hi-spec alloy steel bits with a torsion zone absorb sudden torque spikes to resist breakage, and the set covers the most-used Phillips, square, hex, Torx, and slotted tips.

Features

- Impact-rated torsion bits absorb high-torque shock to reduce breakage
- 50 pieces: Torx, Phillips, square, external hex, slotted, and internal hex tips
- 2in and 5in bit lengths for standard and recessed fasteners
- Ball-end tips ease engagement at an angle
- Backed by the Titan Limited Lifetime Warranty



Torsion Impact Bit Set						
Part Number	Pcs.	Drive Size	Tip Type	Size	Set Includes	Price
T16251	50	1/4in	⊕ Phillips	(2) #2 x 2in, (2) #2 x 5in, (2) #3 x 2in	(6) Phillips bits: ((2) #2 x 2in, (2) #2 x 5in, (2) #3 x 2in), (2) square bits: (#2 x 2in, #3 x 2in), (5) 2in metric external hex bits: (4mm, 5mm, 5.5mm, 6mm, and 8mm), (5) 2in imperial external hex: (5/32in, 3/16in, 7/32in, 1/4in, and 5/16in), (7) 2in Torx bits: (T10, T15, T20, T25, T27, T30, T40), (4) 5in Torx bits: (T25, T27, T30, and T40), (5) 5in metric external hex with ball-end tip: (4mm, 5mm, 5.5mm, 6mm, and 8mm), (5) 5in imperial external hex with ball-end tip: (5/32in, 3/16in, 7/32in, 1/4in, and 5/16in), (1) slotted bit: 3/16 x 2in, (2) 2-1/2in adapters: (1/4in x 1/4in, 1/4in x 3/8in), (1) 2-3/4in adapter: 1/4in x 1/2in, (2) 6in adapters: (1/4in x 1/4in, 1/4in x 3/8in), (2) chucks: (1/4in x 2-1/2in, 1/4in x 6in), (3) 2-1/2in impact nut setters: (1/4in, 5/16in, and 3/8in), plastic storage case	\$73.00
			⊖ Slotted	2in: 3/16in		
			□ Square	#2 x 2in, #3 x 2in		
			⊕ External Hex	2in: 5/32, 3/16, 7/32, 1/4, 5/16in		
				2in: 4, 5, 5.5, 6, 8mm		
				5in: 5/32, 3/16, 7/32, 1/4, 5/16in		
				5in: 4, 5, 5.5, 6, 8mm		
			⊕ Internal Hex	2.5in: 1/4, 5/16, 3/8in (impact nut setters)		
			⊕ Torx	2in: T10, T15, T20, T25, T27, T30, T40		
				5in: T25, T27, T30, and T40		
			Adapters	2.5in: 1/4in x 1/4in, 1/4in x 3/8in		
				2.75in: 1/4in x 1/2in		
			Chucks	6in: 1/4in x 1/4in, 1/4in x 3/8in		
				1/4in x 2-1/2in, 1/4in x 6in		