



Torque Tools



Digital Torque Wrenches

Titan digital torque wrenches signal target torque with LED, vibration and an audible tone, so you know the instant you've hit spec. A reversible, backlit LCD reads five torque units, and a 72-tooth quick-release ratchet head keeps work moving in tight spaces.

Features

- LED, vibration and audible alerts as you approach and reach your target torque
- Reversible, backlit LCD reads five torque units: ft-lb, lb-in, N-m, kg-cm, and kg-m
- 72-tooth reversible ratchet head with quick-release socket retention
- Rubberized non-slip handle for secure control
- Accurate to $\pm 4\%$ per DIN ISO 6789, with a certificate of calibration included
- Enters sleep mode after 3 min of inactivity



Torque Wrenches & Adapters							
Part Number	Product Image	Drive	Overall Length	Set-Point Range	Accuracy	Includes	Price
T23130		1/2in	21.0in [533mm]	30–260 lb-ft	$\pm 4\%$ (DIN ISO 6789)	(2) AAA batteries, storage case, instruction manual, certificate of calibration	\$191.00
T23137		1/2in	16.5in [418mm]	30–150 lb-ft	$\pm 4\%$ (DIN ISO 6789)	(2) AAA batteries, storage case, instruction manual, certificate of calibration	\$144.00