


CT-007-048-24-0 Cut Sheet



BLOCK control transformer, open core, 75 VA, 1-phase, 240/480 VAC, 24 VAC secondary, 50/60 Hz, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CT-007-048-24-0>

Technical Specifications

Brand	BLOCK
Series	CT
Item	Transformer
Transformer Type	Control
Core Type	Open
Power Rating	75 VA
Number of Phases	1
Primary Voltage	240/480 VAC
Secondary Voltage	24 VAC
Frequency	50/60 Hz
Fused	No
Electrostatic Shield	No
Mounting	Panel
Connection	Screw terminals

Agency Approvals

UL Recognized File #	E103521 Displayed as Type/Model EI
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CT-007-048-24-0.pdf>
See store item page for other formats.