



WEG ELECTRIC S PREMIUM EFFICIENCY AC INDUCTION MOTOR, GENERAL PURPOSE, INVERTER RATED & HAZARDOUS LOC & BRAKE, 10HP, 3-PH, 208-230/460 VAC, 1800RPM, TEFC, 215TC FRAME, ROLLED STEEL, C-FACE MOUNT

01018ET3EBMR215TC-S

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
2/14/2024

SHEET 1 OF 1