



M.G.M. ELECTRIC MOTORS BAX IE3 PREMIUM EFFICIENCY AC INDUCTION MOTOR, GENERAL PURPOSE, INVERTER RATED AND BRAKE, 1HP, 3-PHASE, 230/460 VAC, 1800RPM, TEFC, IEC 80 (NEMA 56C FLANGE) FRAME, ALUMINUM, C-FACE MOUNT, INTEGRATED BRAKE ASSEMBLY INCLUDED

18IC

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
6/3/2024

SHEET 1 OF 1