



M.G.M. ELECTRIC MOTORS BAX IE3 PREMIUM EFFICIENCY AC INDUCTION MOTOR, GENERAL PURPOSE, INVERTER RATED AND BRAKE, 3HP, 3-PHASE, 230/460 VAC, 1800RPM, TEFC, IEC 100 (NEMA 182TC FLANGE) FRAME, ALUMINUM, C-FACE MOUNT, INTEGRATED BRAKE ASSEMBLY INCLUDED					181Y		AutomationDirect.com 1-800-633-0405	
	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	inch [mm]	LATEST VERSION 6/3/2024	SHEET 1 OF 1