



M.G.M. ELECTRIC MOTORS BAX IE3 PREMIUM EFFICIENCY AC INDUCTION MOTOR, GENERAL PURPOSE, INVERTER RATED AND BRAKE, 3HP, 3-PHASE, 230/460 VAC, 1800RPM, TEFC, IEC 100 FRAME, ALUMINUM, D-FLANGE/REMOVABLE RIGID BASE (B35) MOUNT, INTEGRATED BRAKE ASSEMBLY INCLUDED

18Q7

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
6/4/2024

SHEET 1 OF 1