



LEVER, IN-LINE, 2 OPENINGS, COPPER CONDUCTOR, 20-12 AWG SOLID, 18-12 AWG STRANDED, 20A, 600V, POLYCARBONATE HOUSING, TRANSPARENT/ORANGE. PACKAGE OF 60.

WAGO SPLICING CONNECTOR

221-2401

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
11/6/2024

SHEET 1 OF 1