



FINGER-SAFE, 115A, 1-POLE, LINE SIDE: 1 OPENING ACCEPTS 2 AWG TO 8 AWG, LOAD SIDE: 10 OPENINGS ACCEPT 4 AWG TO 14 AWG, PANEL OR 35MM DIN RAIL MOUNT, UL 1059 RECOGNIZED.

FTG ENCLOSED TERMINAL BLOCK

38676

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
7/23/2024

SHEET 1 OF 1