



SENSY BENDING BEAM LOAD CELL, 1102 LB/500 KG, +/- 0.3% OF FULL SCALE ACCURACY, VOLTAGE SIGNAL RANGE(s) OF 1.8-2.2 MV/V, 3-12 VDC, STAINLESS STEEL, IP67, 26.2FT/8M INTEGRAL 4-WIRE SHIELDED CABLE

5510-500KG-A3-K

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
11/19/2024

SHEET 1 OF 1