



MECHANICALLY OPERATED DIRECTIONAL CONTROL VALVE, 5-PORT (4-WAY), 2-POSITION, UNIDIRECTIONAL ROLLER LEVER, SPRING RETURN, 1/8IN FEMALE NPT INLET(S), 1/8IN FEMALE NPT OUTLET(S), 1/8IN FEMALE NPT EXHAUST(S), CV=0.55.

METAL WORK DIRECTIONAL CONTROL VALVE

7001000610U

AutomationDirect.com
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	mm [inch]	LATEST VERSION 2/8/2024	SHEET 1 OF 1
--	--------------	-----------------	--	--------------------------------------	--	--------------	----------------------------	--------------