



MECHANICALLY OPERATED DIRECTIONAL CONTROL VALVE, 3-PORT (3-WAY), 2-POSITION, N.C., PILOT-ASSISTED ADJUSTABLE ROLLER LEVER, SPRING RETURN, 1/8IN FEMALE NPT INLET(S), 1/8IN FEMALE NPT OUTLET(S), 1/8IN FEMALE NPT EXHAUST(S), CV=0.55.

## METAL WORK DIRECTIONAL CONTROL VALVE

7001000900U

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
2/8/2024

SHEET 1 OF 1