



- | | |
|----------------------------------|-----------------------------------|
| 1.) BRACKET MOUNTING HOLES | 7.) POWER - I/O CONNECTOR |
| 2.) POWER ON LED | 8.) LENS |
| 3.) ETHERNET CONNECTION LED | 9.) LED AIMING SYSTEM |
| 4.) 90° ROTATING CONNECTOR BLOCK | 10.) RED SPOT (NO GOOD) |
| 5.) HMI INTERFACE | 11.) GREEN SPOT (GOOD) |
| 6.) ETHERNET CONNECTOR | 12.) WHITE POLARIZED ILLUMINATORS |

DATALOGIC SMART-VS SERIES VISION SENSOR, 50-150MM OPERATING DISTANCE, 19 DEGREE VIEWING ANGLE, 320 X 240 OPTICAL RESOLUTION, POLARIZED WHITE LED, IP65 IP67, (3) PUSH-PULL, NPN OR PNP OUTPUT, (1) 17-PIN M12 QUICK-DISCONNECT AND (1) 8-PIN M12 ETHERNET X-CODED.

959971320

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
4/22/2022

SHEET 1 OF 1