



IRONHORSE ACG SERIES AC GENERAL PURPOSE DRIVE, ENCLOSED, 230 VAC, 2HP WITH 3-PHASE INPUT, 1HP WITH 1-PHASE INPUT, SVC OR V/Hz MODE, B FRAME, RS-485, MODBUS, 100KA SCCR. OPTIONAL ETHERNET/IP AND MODBUS TCP CARD AVAILABLE

ACG-22P0

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
3/27/2024

SHEET 1 OF 1