



FINGER-SAFE, 760A, 1-POLE, LINE SIDE: 2 OPENINGS ACCEPT 500 MCM TO 4 AWG CU/AL, LOAD SIDE: 4 OPENINGS ACCEPT 4/0 AWG TO 6 AWG CU/AL, DIN RAIL OR PANEL MOUNT, UL 1953 LISTED.

PENN UNION OPEN POWER DISTRIBUTION BLOCK

APDB-24-500-1

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
6/25/2024

SHEET 1 OF 1