



TECHNICAL INFORMATION

- 1.) SENSING SURFACE
- 2.) POTENTIOMETER
- 3.) LED FUNCTION INDICATOR
- 4.) N.O. OR N.C. SELECTABLE
- 5.) PNP OR NPN SELECTABLE



ISOMETRIC VIEW



BALLUFF CAPACITIVE PROXIMITY SENSOR, ROUND, 50MM DIAMETER X 10MM BODY, POLYOXYMETHYLENE (POM) HOUSING, TOP SENSING, NPN/PNP, N.O./N.C. SELECTABLE, 25MM SENSING DISTANCE, FLUSH, 50 HZ SWITCHING FREQUENCY, IP65, 3-PIN M8 QUICK-DISCONNECT.

BCS003L

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
7/25/2023

SHEET 1 OF 1