



# TECHNICAL INFORMATION

- 1.) SENSING SURFACE
- 2.) HOUSING
- 3.) COVER
- 4.) POTENTIOMETER
- 5.) LED POWER
- 6.) LED FUNCTION INDICATOR



ISOMETRIC VIEW

BALLUFF CAPACITIVE PROXIMITY SENSOR, TUBULAR, 30MM DIAMETER X 87MM BODY, POLYBUTYLENE TEREPHTHALATE HOUSING, PNP, N.O./N.C. SELECTABLE, 20MM SENSING DISTANCE, FLUSH, 100 HZ SWITCHING FREQUENCY, IP66, 4-PIN M12 QUICK-DISCONNECT.

**BCS004M**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
7/21/2023

SHEET 1 OF 1