



ISOMETRIC VIEW

BALLUFF CAPACITIVE PROXIMITY SENSOR, TUBULAR, 12MM DIAMETER X 60MM BODY, STAINLESS STEEL HOUSING, NPN/PNP, N.C., 5MM SENSING DISTANCE, FLUSH, 100 HZ SWITCHING FREQUENCY, IP67, 4-PIN M12 QUICK-DISCONNECT.

**BCS017L**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
7/20/2023

SHEET 1 OF 1