



BALLUFF ETHERNET/IP IO-LINK MASTER, (8) IO-LINK CAPABLE I/O POINTS, UP TO (16) DISCRETE I/O POINTS, IO-LINK V1.1.3, 9A, 2A/PORT, DIE-CAST ZINC NICKEL-PLATED HOUSING, IP67, -25 TO 70 DEG C

BN100HM

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
2/5/2025

SHEET 1 OF 1