



LAUMAS TENSION AND COMPRESSION LOAD CELL, 2204 LB/1000 KG, +/- 0.02% OF FULL SCALE ACCURACY, VOLTAGE SIGNAL
 RANGE(S) OF 2 MV/V, 3-15 VDC, STAINLESS STEEL, IP68, 32.8FT/10M INTEGRAL 6-WIRE SHIELDED CABLE

CTL1000

AutomationDirect.com
 1-800-633-0405



3rd
 ANGLE

NOT TO
 SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
 DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
 FOR PART DESIGN

UNLESS OTHERWISE
 SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
 11/5/2024

SHEET 1 OF 1