



ISOMETRIC VIEW

CONTRINEX INDUCTIVE PROXIMITY SENSOR, TUBULAR, 30MM DIAMETER X 75MM BODY, 304 STAINLESS STEEL HOUSING, NPN, N.O., 10MM SENSING DISTANCE, FLUSH, 200 HZ SWITCHING FREQUENCY, IP67, PIGTAIL.

DW-HD-601-M30-411

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
9/29/2022

SHEET 1 OF 1