



ISOMETRIC VIEW



M12X1.0 HEX NUT  
DETAIL VIEW

ACHIEVE PHOTOELECTRIC SENSOR, TUBULAR, THREADED, METAL HOUSING, THROUGH-BEAM RECEIVER, 4M SENSING DISTANCE, 10-30 VDC OPERATING VOLTAGE, SELECTABLE LIGHT-ON/DARK-ON, PNP, 4-WIRE, PIGTAIL.

**FDMR-0P-1A**

AutomationDirect.com  
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	<b>mm</b> [inch]	LATEST VERSION 7/31/2024	SHEET 1 OF 1
--	--------------	-----------------	--	--------------------------------------	--	---------------------	-----------------------------	--------------