



FINGER-SAFE, 85A, 1-POLE, LINE SIDE: 3 OPENINGS ACCEPT 6 AWG TO 16 AWG, LOAD SIDE: 12 OPENINGS ACCEPT 8 AWG TO 16 AWG, DIN RAIL OR PANEL MOUNT, UL 1059 RECOGNIZED.

GLADIATOR ENCLOSED TERMINAL BLOCK			GPB1-85P1-15S			AutomationDirect.com 1-800-633-0405	
3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	mm [inch]	LATEST VERSION 8/5/2024	SHEET 1 OF 1