



FINGER-SAFE, 115A, 3-POLE, LINE SIDE: 1 OPENING ACCEPTS 2 AWG TO 18 AWG, LOAD SIDE: 1 OPENING ACCEPTS 6 AWG TO 10 AWG & 6 OPENINGS ACCEPT 6 AWG TO 14 AWG, DIN RAIL OR PANEL MOUNT, UL 1059 RECOGNIZED.

# GLADIATOR ENCLOSED TERMINAL BLOCK

# GPB2-115P3-6L

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
8/5/2024

SHEET 1 OF 1