



FINGER-SAFE, 175A, 3-POLE, LINE SIDE: 1 OPENING ACCEPTS 2/0 AWG TO 6 AWG, LOAD SIDE: 1 OPENING ACCEPTS 6 AWG TO 10 AWG & 6 OPENINGS ACCEPT 6 AWG TO 14 AWG, DIN RAIL OR PANEL MOUNT, UL 1059 RECOGNIZED.

GLADIATOR ENCLOSED TERMINAL BLOCK

GPB2-175P3-6L

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
8/5/2024

SHEET 1 OF 1