



FINGER-SAFE, 225A, 1-POLE, LINE SIDE: 1 OPENING ACCEPTS 250 KCMIL TO 2 AWG, LOAD SIDE: 2 OPENINGS ACCEPT 2 AWG TO 14 AWG & 5 OPENINGS ACCEPT 6 AWG TO 14 AWG & 4 OPENINGS ACCEPT 8 AWG TO 14 AWG, DIN RAIL OR PANEL MOUNT.

GLADIATOR ENCLOSED TERMINAL BLOCK			GPB2-255P1-11L			AutomationDirect.com 1-800-633-0405	
3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	mm [inch]	LATEST VERSION 8/5/2024	SHEET 1 OF 1