



FINGER-SAFE, 335A, 1-POLE, LINE SIDE: 1 OPENING ACCEPTS 400 KCMIL TO 3/0 AWG, LOAD SIDE: 2 OPENINGS ACCEPT 2 AWG TO 14 AWG & 5 OPENINGS ACCEPT 6 AWG TO 14 AWG & 4 OPENINGS ACCEPT 8 AWG TO 14 AWG, DIN RAIL OR PANEL MOUNT.

GLADIATOR ENCLOSED TERMINAL BLOCK

GPB2-335P1-11L

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
8/5/2024

SHEET 1 OF 1