



FINGER-SAFE, 80A, 1-POLE, LINE SIDE: 3 OPENINGS ACCEPT 6 AWG TO 14 AWG, LOAD SIDE: 4 OPENINGS ACCEPT 10 AWG TO 14 AWG, DIN RAIL OR PANEL MOUNT, UL 1059 RECOGNIZED.

GLADIATOR ENCLOSED TERMINAL BLOCK

GPB2-80P1-4L

AutomationDirect.com
1-800-633-0405

3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE: mm [inch]	LATEST VERSION 8/5/2024	SHEET 1 OF 1
-----------	--------------	---	-----------------------------------	--	-------------------------	--------------