



2-PORT (2-WAY), 2-POSITION, N.C., STAINLESS STEEL BODY, VITON/PTFE SEAL(s), 3/8IN FEMALE NPT INLET(s), 3/8IN FEMALE NPT OUTLET(s), CV=1.5, 0 PSI MINIMUM OPERATING PRESSURE, 120 VAC OPERATING VOLTAGE, 18mm DIN STYLE WIRING PLUG.

GC SOLENOID VALVE			H401YH02Z1CF5			AutomationDirect.com 1-800-633-0405	
3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	inch [mm]	LATEST VERSION 12/15/2025	SHEET 1 OF 1