



M12 X 1.5MM THREAD TYPE, STAINLESS STEEL, 2000 ML/MIN @ 70 mbar (1 PSI), IP66 IP68, UL TYPE 4X. PACKAGE OF 1.

TIGHTENING TORQUE: 0.5 ± 0.1Nm (4 ± 1ft·lbs)

## BIMED PRESSURE RELIEF VENT PLUG

HBBVP-01L-WNL

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
5/20/2024

SHEET 1 OF 1