



M12 X 1.5MM THREAD TYPE, POLYAMIDE, BLACK, 2000 ML/MIN @ 70 mbar (1 PSI), IP66 IP68, UL TYPE 4X. PACKAGE OF 2.

TIGHTENING TORQUE: $0.5 \pm 0.1\text{Nm}$ ($4 \pm 1\text{ft}\cdot\text{lbs}$)

BIMED PRESSURE RELIEF VENT PLUG

HBVPB-21L-WNL

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
5/20/2024

SHEET 1 OF 1