


ISOMETRIC VIEW



INTERNATIONAL POWER REGULATED LINEAR POWER SUPPLY, 5 VDC @ 6A/30W AND 12-15 VDC @ 2.5A/30W,
120/240 VAC NOMINAL INPUT, 1-PHASE, OPEN FRAME, ALUMINUM HOUSING, CHASSIS MOUNT, TURRET TERMINALS.

IHCC512

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
5/18/2023

SHEET 1 OF 1