



INTERNATIONAL POWER REGULATED LINEAR POWER SUPPLY, 5 VDC @ 2A/10W, 12 OR 15 VDC @ 0.4A/6W AND -5, -12 OR -15 VDC @ 0.4A/6W, 120/240 VAC NOMINAL INPUT, 1-PHASE, OPEN FRAME, ALUMINUM HOUSING, CHASSIS MOUNT, TURRET TERMINALS.

IHTAA-16W

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
5/18/2023

SHEET 1 OF 1