



TECHNICAL SPECIFICATIONS

SLPC [MM]	200
US [USEFUL STROKE]	200
MS [MECHANICAL STROKE]	203
L [TOTAL LENGTH]	301

ISOMETRIC VIEW



PROSENSE POTENTIOMETER LINEAR POSITION SENSOR, PIVOTING SLIDE, 200MM STROKE, 18MM DIAMETER X 248MM BODY, ROD EYES MOUNT, PIGTAIL, 3.2FT/1M CABLE LENGTH.

LCR-18P-0200-C5-1A

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
1/9/2025

SHEET 1 OF 1