


| | |
|--------------------------|-----|
| SLPC [MM] | 400 |
| US [USEFUL STROKE] | 400 |
| MS [MECHANICAL STROKE] | 403 |
| L [TOTAL LENGTH] | 501 |



MECHANICAL STROKE

403.0
[15.87]

M5

EXTENDED

±5MM ADJUSTABLE LENGTH

