



TECHNICAL SPECIFICATIONS

SLPC [MM]	130
US [ USEFUL STROKE ]	130
MS [ MECHANICAL STROKE ]	134
L [ TOTAL LENGTH ]	302




ISOMETRIC VIEW



EXTENDED

±3MM ADJUSTABLE LENGTH



RETRACTED

PROSENSE POTENTIOMETER LINEAR POSITION SENSOR, PIVOTING SLIDE, 130MM STROKE, 38MM DIAMETER X 233MM BODY, ROD EYES MOUNT, 8MM DIN 43650 FORM C.

LCR-38P-0130-C5-C1

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
1/14/2025

SHEET 1 OF 1