



# TECHNICAL SPECIFICATIONS



SLPC [MM]	30
US [ USEFUL STROKE ]	30
MS [ MECHANICAL STROKE ]	34
L [ TOTAL LENGTH ]	169




EXTENDED



RETRACTED



ISOMETRIC VIEW



DETAIL A  
SCALE 1 : 1

PROSENSE POTENTIOMETER LINEAR POSITION SENSOR, FIXED SLIDE, 30MM STROKE, 33 X 33 X 110MM BODY, CHANNEL MOUNT, 18MM DIN 43650 FORM A.

**LSR-33P-0030-A5-C1**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
**[inch]**

LATEST VERSION  
1/10/2025

SHEET 1 OF 1