


# TECHNICAL SPECIFICATIONS

SLPC [MM]	750
US [ USEFUL STROKE ]	750
MS [ MECHANICAL STROKE ]	754
L [ TOTAL STROKE ]	889

ISOMETRIC VIEW



MECHANICAL STROKE

754.0  
[29.69]

M6

EXTENDED

920.9  
[36.25]

830.0  
[32.68]

63.7  
[2.51]

RETRACTED

56.5  
[2.22]

42.5  
[1.67]

109.7  
[4.32]

665.0  
[26.18]

82.5  
[3.25]

15.6  
[0.61]

25.2  
[0.99]

40.8  
[1.61]

33.0  
[1.30]

54.3  
[2.14]

M4X16.0  
(4X)

10.0  
[0.39]

7.5  
[0.30]  
SYM.

M-SLOT  
4.6X5.6  
(4X)

1.1  
[0.04]

DETAIL B  
SCALE 2 : 2.5

PROSENSE POTENTIOMETER LINEAR POSITION SENSOR, FIXED SLIDE, 750MM STROKE, 33 X 33 X 830MM BODY, CHANNEL MOUNT, 18MM DIN 43650 FORM A.

LSR-33P-0750-D10-C1

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
1/14/2025

SHEET 1 OF 1