



EVER MOTION SOLUTIONS DC OPEN LOOP MICROSTEPPING STEPPER DRIVE, 4.2A PER PHASE, 2-PHASE OUTPUT, 100-240 VAC, BIPOLAR, POSITION MODE, 200 TO 65536 STEPS PER REVOLUTION, (1) RJ11 PORT(S)

**LW3A9030N2A1-00**

AutomationDirect.com  
1-800-633-0405

3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	<b>mm</b> [inch]	LATEST VERSION 1/20/2025	SHEET 1 OF 1
-----------	--------------	---	-----------------------------------	---------------------------------------	---------------------	-----------------------------	--------------