



EVER MOTION SOLUTIONS DC OPEN LOOP MICROSTEPPING STEPPER DRIVE, 10A PER PHASE, 2-PHASE OUTPUT, 24-80 VDC, BIPOLAR, POSITION MODE, 200 TO 51200 STEPS PER REVOLUTION

LW3D3070N0A1-00

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
1/20/2025

SHEET 1 OF 1