



EVER MOTION SOLUTIONS DC OPEN/CLOSED LOOP MICROSTEPPING STEPPER DRIVE, 10A PER PHASE, 2-PHASE OUTPUT, 24-75 VDC, BIPOLAR, POSITION MODE, 200 TO 65536 STEPS PER REVOLUTION, (1) 4-PIN TERMINAL PORT(S). REQUIRES LW4D3KIT-C0 CONNECTOR KIT OR LW4D3KIT-050 CABLE KIT

LW4D3070N2I1-00

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
1/20/2025

SHEET 1 OF 1