



IronHorse MTR SERIES PREMIUM EFFICIENCY AC INDUCTION MOTOR, CENTRIFUGAL JET PUMP, 3HP, 3-PH, 208-230/460 VAC, 3600RPM, TEFC, 56J FRAME, ROLLED STEEL, REMOVABLE BASE/C-FACE MOUNT

MTRJP-003-3BD36J

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
4/25/2022

SHEET 1 OF 1