



IronHorse MTR SERIES PREMIUM EFFICIENCY AC INDUCTION MOTOR, CENTRIFUGAL JET PUMP, 1-1/2HP, 3-PH, 208-230/460 VAC, 3600RPM, TEFC, 56J FRAME, ROLLED STEEL, REMOVABLE BASE/C-FACE MOUNT

**MTRJP-1P5-3BD36J**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**inch**  
**[mm]**

LATEST VERSION  
4/25/2022

SHEET 1 OF 1