



2-PORT (2-WAY), 2-POSITION, N.C., LEAD-FREE BRASS BODY, EPDM RUBBER SEAL(s),
 1/2IN FEMALE NPT INLET(s), 1/2IN FEMALE NPT OUTLET(s), CV=4.3, 120 VAC
 OPERATING VOLTAGE, 8W, NSF/ANSI 61.

GC VALVES POTABLE WATER SOLENOID VALVE

NS711YH02C9DG1

AutomationDirect.com
 1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
 DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
 PART DESIGN

UNLESS OTHERWISE
 SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
 2/18/2025

SHEET 1 OF 1