



2-PORT (2-WAY), 2-POSITION, N.C., LEAD-FREE BRASS BODY, EPDM RUBBER SEAL(s),
1-1/4IN FEMALE NPT INLET(s), 1-1/4IN FEMALE NPT OUTLET(s), CV=22, 120 VAC
OPERATING VOLTAGE, 8W, NSF/ANSI 61.

GC VALVES POTABLE WATER SOLENOID VALVE

NS711YH02C9GJ2

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
2/18/2025

SHEET 1 OF 1