


ISOMETRIC VIEW



ACHIEVE INDUCTIVE PROXIMITY SENSOR, TUBULAR, 8MM DIAMETER X 45MM BODY, 304 STAINLESS STEEL HOUSING, PNP, N.O. OUTPUT, 2.5MM SENSING DISTANCE, NON-FLUSH, 4.5 KHZ SWITCHING FREQUENCY, IP67, 3-PIN M8 QUICK-DISCONNECT.

PAE-AP-2F

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
10/11/2023

SHEET 1 OF 1