



2-PORT (2-WAY), 2-POSITION, N.C., BRASS BODY, VITON SEAL(S), 1IN FEMALE NPT INLET(S), 1IN FEMALE NPT OUTLET(S), CV=13, 5 PSI MINIMUM OPERATING PRESSURE, 24 VDC OPERATING VOLTAGE, 18mm DIN STYLE WIRING PLUG.

GC VALVES SOLENOID VALVE

S211YH16V5FG9

AutomationDirect.com
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	inch [mm]	LATEST VERSION 12/15/2025	SHEET 1 OF 1
--	-----------	--------------	---	---------------------------------	---------------------------------------	----------------------------	------------------------------	--------------